



Comitrol® Processor Slant Model 3600

Controlled Particle Size Reduction



Comitrol® Processor
Model 3600 Slant



COMITROL® PROCESSOR MODEL 3600 SLANT

SPECIFICATIONS

Comitrol® Processor Model 3600 Slant:

Length: 35.69" (907 mm)
Width: 29.21" (742 mm)
Height: 38.64" (981 mm)
Net Weight: 400 lb (181 kg)
Motor: Impeller - 10 HP (7.5 kW)

APPLICATIONS


The compact size of the Comitrol Processor Slant Model 3600 makes the machine ideal for a wide range of small volume to high capacity production environments.

Processors benefit from the wide selection of cutting heads and impellers that are available for diverse applications such as chopping, flake cutting, granulating, pureeing, and emulsifying.

Foods such as meats, poultry, fruits, vegetables, and cheeses can be processed as well as many chemical and pharmaceutical products. The machine features continuous operation for uninterrupted production, and is designed for easy cleanup and maintenance.

OPERATING PRINCIPLE

Product is guided to the high speed, rotating impeller [1]. When product reaches the impeller, it revolves at a high speed inside the cutting head. Centrifugal force propels the product outward past the cutting edges of the stationary reduction head. The cutting head [2] has uniformly spaced thin horizontal bars, or separators [3]. Small portions of product projecting into the spaces between the separators are cut off into flakes by spaced columns of vertical knives [4]. These flakes quickly travel outward and away from the cutting head. The wall surfaces between the vertical knives are relieved to eliminate rubbing friction that would produce heat.




CUTTING HEAD ASSEMBLY

TYPES OF CUTS

Particle sizes ranging from coarse to fine emulsions are possible. To ensure the proper combination of cutting parts, Urschel Laboratories, Inc. recommends your product be tested in one of our worldwide Product Test Cutting Facilities free-of-charge to find the most efficient solution to your size reduction needs.

If your product application is not mentioned on this page, contact your local Urschel representative to determine the most effective solution to your size reduction needs.

(over)



You Are Invited to Test Cut Your Product

Urschel Laboratories has a complete network of test facilities and experienced service and sales representatives around the world ready to work for you on any size reduction application. Contact your local Urschel Laboratories' representative to schedule a comprehensive, no-obligation test today at www.urschel.com.



URSCHEL®
THE SIZE REDUCTION SPECIALISTS

www.urschel.com | info@urschel.com