



designed to work perfectly



UTC 80/KD

/// Data Sheet

The ULTRA-TURRAX® UTC is a high-performance dispersing machine used for the production of a variety of emulsions and suspensions in batch operations. Using the rotor-stator principle, the UTC is best suited for applications that cannot be accomplished using conventional stirring methods. The UTC machine stator is mounted to the shaft tube and is capable of processing of media with a viscosity of up to 5.000 mPas. The preferred installation positions for the UTC are: diagonal from above, diagonal from the side or vertical off-centre.

The UTC series is available with two different types of flanges KT for installation on open vessels and KD for closed vessels. The UTC for open vessels can be offered with suitable floor, wall or mobile stands.



designed to work perfectly

The rotating shaft is sealed with either a lip (KT) or mechanical (KD) seal. For operations under pressures of up to 10 bar or for the processing of abrasive media, the ULTRA-TURRAX® is equipped with a mechanical seal.

The description of the machine contains the following information:

Machine type

Generator type

Size of the machine (outer diameter of the dispersing tool)

Number of toothed rings of the dispersing tool

Type of seal

Type of flange

Example: The UTC TP 115/4-KT/KD is an ULTRA-TURRAX® UTC machine with a TP 115/4 generator (four toothed rings, outer diameter of 115 mm). This machine is equipped with a lip seal (KT) and designed for mounting on closed vessels (KD).



designed to work perfectly

Technical Data

Batch size max. (H2O)	40 Gal
Viscosity, max.	5000 mPas
Process pressure (max.)	10 bar
Vacuum, max	100 mbar
Process temperature, max.	120 °C
Dispersing tool	rotor-stator
Tip speed	12 m/s
Rotor rotational speed	3600 rpm
Motor power, standard	3 HP
Motor power max.	3 kW
Type of seal	single acting mechanical seal
Built-in length, standard	650 mm
Built-in length, max.	965 mm
Weight approx.	105 lbs

